

a measurable difference...



Melt Flow Indexer

Model: M0004

The Melt Flow Indexer is a dead-weight extrusion plastometer. It consists of a thermostatically controlled melting chamber (the barrel) in which the polymer under test is heated and from which it is extruded through a standard die under standard conditions of load, which is, of course, made up of the combined weights of the extrusion piston and the loose weight both of which are carefully calibrated to well within the most stringent limits.

Application:

- Plastics

Features:

- **Barrel:** Precision ground and honed. Manufactured from high grade tool steel for longer life.
50.8 mm outside diameter
9.55 mm inside diameter
162 mm long
- **Temperature:** The temperature of the barrel is controlled by the Precision Digital Temperature Controller.
Temperature Range: 100° - 300°C, ± 0.1°C.
- **Die:** Tungsten Carbide:
8 mm long
9.47 mm overall diameter
2.096 mm internal diameter
The alternative Standard die in BS 2782 method 1050 with a bore diameter of 1.181 mm is also available on request.
- **Piston:**
Diameter: 9.47 mm
Weight - 100 gm.
- **Piston Weights:**
4.9 Kg weight (1)
2.06 Kg weight (1)
- **Sample Cut Off Knife (1)**
- **Die Remover (1)**
- **Die Cleaner (1)**
- **Cleaning Tool (1)**
- **Filler Tool (1)**
- **Level (1)**



Standards:

- BS2782
- ASTM D1238: Procedure A
- ISO 1133

Connections:

- **Electrical:** 220/240 VAC @ 50 HZ or 110 VAC @ 60 HZ
(please specify when ordering)

Dimensions:

- **H:** 480mm
- **W:** 430mm
- **D:** 270mm
- **Weight:** 27kg

10-11 Colrado Court, Hallam, Victoria 3803 Australia.

Phone: +61 3 9708 6885 Fax: +61 3 9708 6770

Website: www.idminstruments.com.au Email: idm@idminstruments.com.au

All sizes and dimensions shown on this data sheet are averages only and images are as accurate as the medium allows. Products and details shown may change without notice as IDM Instruments reserves the right to make alterations to its product range from time to time.

a measurable difference...



Melt Flow Indexer

Options:

- Calibration Certificate
- Spare Die

Procedural Conditions:

Material	Condition	
Acetals (copolymer and homopolymer)	190/2.16	190/1.05
Acrylics	230/1.2	230/3.8
Acrylonitrile-butadiene-styrene	200/5.0	230/3.8
	220/10	
Acrylonitrile/butadiene/styrene/polycarbonate blends	230/3.8	250/1.2
	265/3.8	265/5.0
Cellulose esters	190/0.325	190/2.16
	190/21.60	210/2.16
Ethylene-chlorotrifluoroethylene copolymer	271.5/2.16	
Ethylene-tetrafluoroethylene copolymer	297/5.0	
Nylon	275/0.325	235/1.0
	235/2.16	235/5.0
	275/5.0	
Perfluoro (ethylene-propylene) copolymer	372/2.16	
Perfluoroalkoxyalkane	372/5.0	
Polycaprolactone	125/2.16	80/2.16
Polychlorotrifluoroethylene	265/12.5	
Polyethylene	125/0.325	125/2.16
	250/1.2	
	190/0.325	190/2.16
	190/21.60	190/10
	310/12.5	
Polycarbonate	300/1.2	
Polymonochlorotrifluoroethylene	265/21.6	
	265/31.6	
Polypropylene	230/2.16	
Polystyrene	200/5.0	230/1.2
	230/3.8	190/5.0
Polyterephthalate	250/2.16	210/2.16
	285/2.16	
Poly (vinyl acetal)	150/21.6	
Poly (vinylidene fluoride)	230/21.6	
	230/5.0	
Poly (phenylene sulfide)	315/5.0	
Styrene acrylonitrile	220/10	230/10
	230/3.8	
Styrenic Thermoplastic Elastomer	190/2.16	200/5.0
Thermoplastic Elastomer-Ether-Ester	190/2.16	220/2.16
	230/2.16	240/2.16
		250/2.16
Thermoplastic Elastomers (TEO)	230/2.16	
Vinylidene fluoride copolymers	230/21.6	
	230/5.0	

These conditions have been found satisfactory for the materials listed

10-11 Colrado Court, Hallam, Victoria 3803 Australia.

Phone: +61 3 9708 6885

Fax: +61 3 9708 6770

Website: www.idminstruments.com.au

Email: ids@idminstruments.com.au

All sizes and dimensions shown on this data sheet are averages only and images are as accurate as the medium allows. Products and details shown may change without notice as IDM Instruments reserves the right to make alterations to its product range from time to time.